

Product data sheet

Characteristics

BP539

Max 4 Link Bars, Strip Connectors, 10A, Plastic
Light Duty, 12 Terminal Available Bk Or Tr



Main

Product brand	Clipsal
Range of product	Blue Point

Complementary

Cable cross section	4 mm ² fine stranded without cable end sleeve
[In] rated current	10 A
Connector type	1 screw terminals 2 screw terminals
Number of poles	12
Mounting support	Panel
Material	Flameproof high-impact polystyrene: insulation
Width	20 mm grid pattern:
Minimum mounting height	16 mm
Length	129 mm



Environment



Ambient air temperature for operation	100 °C
Standards	CS/840/N

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.6 cm
Package 1 Width	1.5 cm
Package 1 Length	10.6 cm
Package 1 Weight	0.034 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations