

Product data sheet

Characteristics

BP539

CONNECTOR STRIP 10A



Main

Product brand	Clipsal
Range of product	Blue Point

Complementary

Cable cross section	4 mm ² fine stranded without cable end sleeve
[In] rated current	10 A
Connector type	1 screw terminals 2 screw terminals
Number of poles	12
Mounting support	Panel
Material	Flameproof high-impact polystyrene: insulation
Width	20 mm grid pattern:
Minimum mounting height	16 mm
Length	129 mm




Environment

Ambient air temperature for operation	100 °C
Standards	CS/840/N

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.034 kg
Package 1 Height	16 mm
Package 1 width	15 mm
Package 1 Length	106 mm

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration