

Product data sheet

Characteristics

BP542

CONNECTOR STRIP 30A



Main

Product brand	Clipsal
Range of product	Blue Point

Complementary

Cable cross section	16 mm ² fine stranded without cable end sleeve
[In] rated current	30 A
Connector type	1 screw terminals 2 screw terminals
Number of poles	12
Mounting support	Panel
Material	Phenolic: insulation
Width	29 mm grid pattern:
Minimum mounting height	20 mm
Length	178 mm

Environment

Ambient air temperature for operation	190 °C
Standards	CS/840/N

Packing Units

Package 1 Weight	127 g
------------------	-------

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.