

## Product data sheet

### Characteristics

# BP6

## Clipsal MAX4 Connector Strip, 80A



### Main

Product brand	Clipsal
Range of product	Blue Point

### Complementary

Distance between centers	Hole: 15 mm
Cable cross section	25 mm <sup>2</sup> fine stranded without cable end sleeve
[In] rated current	110 A
Connector type	1 screw terminals 2 screw terminals
Number of poles	6
Mounting support	Panel
Material	Bakelite: insulation
Width	40 mm grid pattern:
Minimum mounting height	25 mm
Length	110 mm




### Environment

Ambient air temperature for operation	190 °C
---------------------------------------	--------

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	4 cm
Package 1 Length	11 cm
Package 1 Weight	168 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

---

RoHS exemption information

 [Yes](#)

---

Environmental Disclosure

 [Product Environmental Profile](#)

---