

Product data sheet

Characteristics

BP6

CONNECTOR STRIP 80A



Main

Product brand	Clipsal
Range of product	Blue Point

Complementary

Distance between centers	Hole: 15 mm
Cable cross section	25 mm ² fine stranded without cable end sleeve
[In] rated current	110 A
Connector type	1 screw terminals 2 screw terminals
Number of poles	6
Mounting support	Panel
Material	Bakelite: insulation
Width	40 mm grid pattern:
Minimum mounting height	25 mm
Length	110 mm




Environment

Ambient air temperature for operation	190 °C
---------------------------------------	--------

Packing Units

Package 1 Weight	168.000 g
Package 1 Height	25.000 mm
Package 1 width	40.000 mm
Package 1 Length	110.000 mm

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration