

Product data sheet

Characteristics

BP6

Connector Strip, Max 4 Link Bars, 80A



Main

Product brand	Clipsal
Range of product	Blue Point

Complementary

Distance between centers	Hole: 15 mm
Cable cross section	25 mm ² fine stranded without cable end sleeve
[In] rated current	110 A
Connector type	1 screw terminals 2 screw terminals
Number of poles	6
Mounting support	Panel
Material	Bakelite: insulation
Width	Grid pattern: 40 mm
Minimum mounting height	25 mm
Length	110 mm




Environment

Ambient air temperature for operation	190 °C
---------------------------------------	--------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	4 cm
Package 1 Length	11 cm
Package 1 Weight	168 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

