

Product data sheet

Characteristics

BP7

CONNECTOR STRIP 20A 12TERM



Main

Product brand	Clipsal
Range of product	Blue Point

Complementary

Distance between centers	Hole: 10.6 mm
Cable cross section	6 mm ² fine stranded without cable end sleeve
[In] rated current	20 A
Connector type	1 screw terminals 2 screw terminals
Number of poles	12
Mounting support	Panel
Material	Bakelite: insulation
Width	25 mm grid pattern:
Minimum mounting height	17 mm
Length	136 mm




Environment

Ambient air temperature for operation	190 °C
---------------------------------------	--------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	66.2 g
Package 1 Height	17 mm
Package 1 width	25 mm
Package 1 Length	139 mm

Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration