

Product data sheet

Characteristics

BSL33VA-WE

Metal Plate Series, Flush Switch, 3 Gang,
250VAC, 10A, Range, BSL Style, Standard,
Vert



Main

Range of product	Metal Plate
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

Complementary

Switch function	2-way 1-way
Number of rocker	3
Device mounting	Flush
Fixing mode	By screws
Surface treatment	Stainless steel
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Actuator	Rocker

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.6 cm
Package 1 Width	9 cm
Package 1 Length	13.5 cm
Package 1 Weight	191 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	12.85 cm
Package 2 Width	4.4 cm
Package 2 Length	8.6 cm
Package 2 Weight	955 g
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	18 cm
Package 3 Width	33.5 cm

Package 3 Length	50 cm
Package 3 Weight	10 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile