

Product data sheet

Characteristics

BVS800I-AZ

UPS, Easy UPS, BVS 800VA, AVR, 230V, Australia



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or component type	Uninterruptible power supply (UPS)
Cable length	1.52 m
Battery type	Lead-acid battery Sealed rechargeable Internal battery
Range of product	Easy UPS 1Ph BVS Series

Complementary

Display type	LED indicator
Transfer time	6 ms typical : 10 ms maximum
Power range	800 VA
Electrical connection	Output: 4 outlet Australian Input: 1 cable
Local signalling	Alarm, distinctive for low battery Alarm, continuous or intermittent tone for overload LCD display for status and alert
Charging time	8 h
Net weight	5.3 kg
Height	9.25 cm
Width	16.05 cm
Depth	30.5 cm

Environment

Relative humidity	0...90 %, non-condensing
Operating altitude	0...1968.3 m
Ambient air temperature for operation	0...40 °C
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Product certifications	CE[RETURN]RCM

Physical

Mounting support	Wall-mount
------------------	------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.362 cm
Package 1 Width	1.422 cm
Package 1 Length	3.734 cm
Package 1 Weight	5.602 kg
SCC14	10731304346460

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	2 years
----------	---------