

Product data sheet

Characteristics

C1252434

MSC Chassis 3PH, Acti9, 400A, 27mm for
C120 MCB 24 poles, Dual Feed

Main

Range	Acti9
Device short name	MSC 27
Product or component type	Chassis
Device application	Distribution

Complementary

Range compatibility	Acti 9 Acti9 Isobar B distribution board
[In] rated current	400 A
Number of ways	1 way (incomer) - 3P 24 ways (outgoer)
Outgoer Pole capacity	24 x 27 mm
Busbar pitch	27 mm
Length	326 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	24.0 cm
Package 1 Length	62.0 cm
Package 1 Weight	3213.0 g

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.