

## Product data sheet

### Characteristics

# C2015-WE

## Classic C2000 Series, Single Switch Socket Outlet Classic, 250V, 10A



### Main

Range of product	Classic Series C2000
Product brand	Clipsal

### Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3112
-----------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8 cm
Package 1 Width	2.5 cm
Package 1 Length	11.5 cm
Package 1 Weight	87 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	12.8 cm

Package 2 Width	15 cm
Package 2 Length	16.6 cm
Package 2 Weight	0.898 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	26.7 cm
Package 3 Width	35.4 cm
Package 3 Length	45.1 cm
Package 3 Weight	9.548 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>