

Product data sheet

Characteristics

C2015D4SI-BK

Clipsal C2000 Series Quad Switch Socket Outlet Classic, 250V, 10A, 2 Pole, Safety Shutter



Main

Range of product	Classic Series C2000
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	4 gangs
Pin number	3
Number of power socket outlets	4
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3112
-----------	-------------

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	7.6 cm
Package 1 Length	11.6 cm
Package 1 Weight	0.284 kg
Unit Type of Package 2	CAR
Number of Units in Package 2	50

Package 2 Height	22.5 cm
Package 2 Width	34.8 cm
Package 2 Length	44.5 cm
Package 2 Weight	14.2 kg
Unit Type of Package 3	PAL
Number of Units in Package 3	900
Package 3 Height	95 cm
Package 3 Width	114 cm
Package 3 Length	114 cm
Package 3 Weight	255.6 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information