

## Product data sheet

### Characteristics

# C2015L-WE

## Clipsal C2000 Series Single Switch Socket Outlet Classic, 250V, 10A, Round Earth Pin



### Main

|                  |                      |
|------------------|----------------------|
| Range of product | Classic Series C2000 |
| Product brand    | Clipsal              |

### Complementary

|                                |                         |
|--------------------------------|-------------------------|
| Control type                   | ON/OFF button           |
| Number of gangs                | 1 gang                  |
| Pin number                     | 3                       |
| Number of power socket outlets | 1                       |
| Actuator                       | Switch<br>Rocker        |
| Fixing mode                    | By screws               |
| Local signalling               | Without light indicator |
| Mounting position              | Horizontal              |
| Material                       | Plastic                 |
| Surface finish                 | Glossy                  |
| [Ue] rated operational voltage | 250 V AC                |
| [In] rated current             | 10 A                    |
| Depth                          | 28 mm                   |
| Length                         | 116 mm                  |
| Width                          | 76 mm                   |
| Fixing center                  | 84 mm                   |

### Environment

|           |             |
|-----------|-------------|
| Standards | AS/NZS 3112 |
|-----------|-------------|

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type of Package 1       | Db      |
| Number of Units in Package 1 | 1       |
| Package 1 Height             | 2.5 cm  |
| Package 1 Width              | 7.5 cm  |
| Package 1 Length             | 11.7 cm |
| Package 1 Weight             | 86.0 g  |

## Offer Sustainability

|                            |   |
|----------------------------|---|
| Sustainable offer status   | Green Premium product                         |
| REACH Regulation           | <a href="#">REACH Declaration</a>             |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes   |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>        |
| RoHS exemption information | <a href="#">Yes</a>                           |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a> |