

Product data sheet

Characteristics

C2025-WE

Classic C2000 Series, Twin Switch Socket Outlet Classic, 250V, 10A



Main

Range of product	Classic Series C2000
Product brand	Clipsal

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3112
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	2.5 cm
Package 1 Length	12 cm
Package 1 Weight	104 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	13.4 cm

Package 2 Width	14.6 cm
Package 2 Length	16.4 cm
Package 2 Weight	1.112 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	26.6 cm
Package 3 Width	35.8 cm
Package 3 Length	45.1 cm
Package 3 Weight	11.59 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile