

## Product data sheet

### Characteristics

# C2025LI-WE

## SWITCHED SOCKET TWIN CIRCUIT IDENTIFICATION LIGHTING



### Main

Product or component type	Switched socket
Colour	White electric
Product brand	Clipsal
Range of product	Classic Series C2000
Socket additional information	Round earth

### Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Indicator light
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3112
-----------	-------------

### Packing Units

Package 1 Weight	0.001 kg
Package 1 Height	28.000 mm
Package 1 width	76.000 mm
Package 1 Length	116.000 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>