

Product data sheet

Characteristics

C2025RC10-WE

SWITCHED SOCKET TWIN 10A RCD 10MA



Main

Product or component type	Switched socket
Colour	White electric
Product brand	Clipsal
Range of product	Classic Series C2000

Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Without light indicator
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3112
-----------	-------------

Packing Units

Package 1 Weight	231.000 g
Package 1 Height	60.000 mm
Package 1 width	100.000 mm
Package 1 Length	146.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile