

## Product data sheet

### Characteristics

# C2025SF-WE

## SWITCHED SOCKET TWIN SURGE FILTER



### Main

Range of product	Classic Series C2000
Product brand	Clipsal
Colour	White electric

### Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Rocker Switch
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	28 mm
Length	116 mm
Width	76 mm
Fixing center	84 mm

### Environment

Standards	AS/NZS 3112
-----------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	179.4 g
Package 1 Height	59 mm
Package 1 width	102 mm
Package 1 Length	146 mm

### Offer Sustainability

EU RoHS Directive	Compliant  EU RoHS Declaration
-------------------	---