

Product data sheet

Characteristics

C2030I-WE

SWITCH 1 GANG CIRCUIT IDENTIFICATION

ARCHITRAVE



FAN	HEAT	EXHAUST	LIGHT
WASH	WASTE	TV	COOL
POOL	A.C.	PUMP	STUDY
BATH	ALARM	DECKCH	CHIEF
ZONE 1	ZONE 2	ZONE 3	ZONE 4
FREEZE	M/WAVE	HOB	OVEN
RANGE	RESET	SPA	HAB
AUTO	LOUNGE	KITCHEN	PUMPUS
CONE	RED	BED 1	BED 2
DR	CB	CB	CB

Main

Range of product	Classic Series C2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Switch function	1-pole
Actuator	Rocker
Number of rocker	1
Number of poles	1
Device mounting	Flush
Fixing mode	By screws
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Marking location	Marking on surface

Environment

Standards	AS/NZS 3080-96
-----------	----------------

Packing Units

Package 1 Weight	0.001 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile