

Product data sheet

Characteristics

C2031D32-WE

Clipsal C2000 Series Electric Range Switches

415V, 32A, Double Pole



Main

Range of product	Classic Series C2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate

Complementary

Switch function	2-pole
Number of rocker	1
Number of poles	2
Device mounting	Flush
Fixing mode	By screws
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	415 V AC
Rated current	32 A
Marking	Without marking
Actuator	Rocker

Environment

Standards	AS/NZS 60669.1
-----------	----------------

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	3.3 cm
Package 1 Width	8.4 cm
Package 1 Length	12.1 cm
Package 1 Weight	126.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information

 [Yes](#)

Environmental Disclosure

 [Product Environmental Profile](#)
