

Product data sheet

Characteristics

C2031D32N-WE

SWITCH 1 GANG DOUBLE POLE 32A COOK NEON



Main

| | |
|---------------------|-------------------------------------|
| Range of product | Classic Series C2000 |
| Product brand | Clipsal |
| Device presentation | Basic element with full cover plate |

Complementary

| | |
|--------------------------------|-----------------|
| Switch function | 2-pole |
| Number of rocker | 1 |
| Number of poles | 2 |
| Device mounting | Flush |
| Fixing mode | By screws |
| Surface finish | Glossy |
| Local signalling | neon |
| [Ue] rated operational voltage | 415 V AC |
| Rated current | 32 A |
| Marking | Without marking |
| Actuator | Rocker |




Environment

| | |
|-----------|----------------|
| Standards | AS/NZS 60669.1 |
|-----------|----------------|

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 127 g |
| Package 1 Height | 25 mm |
| Package 1 width | 120 mm |
| Package 1 Length | 75 mm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information |  Yes |

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
