

## Product data sheet

### Characteristics

# C2031E4RUD-WE

## DIMMER UNIVERSAL ISRC 800W



### Main

Range of product	Classic C2000 Series C-Thru
Product brand	Clipsal
Device presentation	Basic element with full cover plate
Dimmer type	Universal
Colour	White electric

### Complementary

Power consumption in VA	10...800 VA
[Ue] rated operational voltage	220...240 V AC
Network frequency	50 Hz
Control type	Rotary knob
Fixing mode	By screws

### Environment

Standards	AS/NZS 3100 IEC 60669-2-1 AS/NZS CISPR 15 IEC 61000-3-2
-----------	--

### Packing Units

Package 1 Weight	218.2 g
------------------	---------

### Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
-------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.