

## Product data sheet

### Characteristics

# C2031H66-WE

Switch C2000 - Assembled - Horizontal - 1-gang - IP 66 - 250 V - 20 A - White Electric



### Main

Range of product	Classic Series C2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

### Complementary

Switch function	1-pole
Number of rocker	1
Number of poles	1
Device mounting	Flush
Fixing mode	By screws
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 AX, fluorescent lamp 20 A
Marking	Without marking
Actuator	Rocker

### Environment

Standards	AS/NZS 60669.1
-----------	----------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	111 g
Package 1 Height	55 mm
Package 1 width	75 mm
Package 1 Length	120 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

---

China RoHS Regulation

 [China RoHS Declaration](#)

---

Environmental Disclosure

 [Product Environmental Profile](#)

---