

Product data sheet

Characteristics

C2031H66-WE

Classic C2000 Series, Flush Switch 1 Gang,
250VAC, 10A, Classic , Horizontal, IP66



Main

Range of product	Classic Series C2000
Product brand	Clipsal
Assembly Type	Basic element with full cover plate and grid

Complementary

Number of poles	1
Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 AX, fluorescent lamp 20 A
Marking	Without marking
Mounting Type	By screws
Surface finish	Glossy
Actuator	Rocker
Switch function	1-pole

Environment

Standards	AS/NZS 60669.1
-----------	----------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	7.5 cm
Package 1 Length	12.0 cm
Package 1 Weight	111.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations