

## Product data sheet

### Characteristics

# C2031H66-WE

Flush Switch, Classic C2000 Series, 1 Gang,  
250VAC, 10A, Horizontal, IP66



#### Main

Range of product	Classic Series C2000
Product brand	Clipsal
Assembly Type	Basic element with full cover plate and grid

#### Complementary

Number of poles	1
Installation Type	Flush
Number Of Switches	1
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 AX, fluorescent lamp 20 A
Marking	Without marking
Mounting Type	By screws
Surface finish	Glossy
Actuator	Rocker
Switch function	1-pole

#### Environment

Standards	AS/NZS 60669.1
-----------	----------------

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	7.5 cm
Package 1 Length	12.0 cm
Package 1 Weight	111.0 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations