

## Product data sheet

### Characteristics

# C2032A-WE

## Classic C2000 Series, Flush Switches

### Architrave Size, Switch 2 Gang 250V 10A



#### Main

Range of product	Classic Series C2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

#### Complementary

Switch function	1-pole
Number of rocker	2
Number of poles	1
Device mounting	Flush
Fixing mode	By screws
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Actuator	Rocker

#### Environment

Standards	AS/NZS 60669.1
-----------	----------------

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.3 cm
Package 1 Width	4.5 cm
Package 1 Length	9.5 cm
Package 1 Weight	48 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	97 cm
Package 2 Width	87 cm
Package 2 Length	166 cm
Package 2 Weight	0.52 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	237 cm

Package 3 Width	203 cm
Package 3 Length	300 cm
Package 3 Weight	5.2 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>