

Product data sheet

Characteristics

C2032AI-WE

Classic C2000 Series, Flush Switch 2 Gang,
250VAC, 10A, Classic



FAN	HEAT	EXHAUST	LIGHT
WASH	WASTE	TV	COOL
POOL	A.C.	PUMP	STUDY
BATH	ALARM	SENSOR	CORRE
ZONE 1	ZONE 2	ZONE 3	ZONE 4
FRIEGE	M/WAVE	HOB	OVEN
RANGE	RESET	SPA	HWS
AUTO	LOUNGE	KITCHEN	HUMIDUS
ZONE	RED	RED 1	RED 2
OS	OB	CB	CB

Main

Range of product	Classic Series C2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

Complementary

Switch function	1-pole
Number of rocker	2
Number of poles	1
Device mounting	Flush
Fixing mode	By screws
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Marking location	Marking on surface
Actuator	Rocker

Environment

Standards	AS/NZS 60669.1
-----------	----------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.001 kg

Offer Sustainability

RECh Regulation	RECh Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.