

Product data sheet

Characteristics

C2032H66-WE

Clipsal C2000 Series Flush Switch 2 Gang,
250VAC, 10A, Classic , Horizontal, IP66



Main

Range of product	Classic Series C2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

Complementary

Switch function	1-pole
Number of rocker	2
Number of poles	1
Device mounting	Flush
Fixing mode	By screws
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 AX, fluorescent lamp 20 A
Marking	Without marking
Actuator	Rocker




Environment

Standards	AS/NZS 60669.1
-----------	----------------

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	5.2 cm
Package 1 Width	7.2 cm
Package 1 Length	12.0 cm
Package 1 Weight	88.0 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration

RoHS exemption information

 [Yes](#)

Environmental Disclosure

 [Product Environmental Profile](#)
