

Product data sheet

Characteristics

C2032V66-WE

Switch C2000 - Assembled - Vertical - 2-gang - IP66 - 250 V - 20 A - White Electric



Main

Range of product	Classic Series C2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

Complementary

Switch function	1-pole
Number of rocker	2
Number of poles	1
Device mounting	Flush
Fixing mode	By screws
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 AX, fluorescent lamp 20 A
Marking	Without marking
Actuator	Rocker

Environment

Standards	AS/NZS 60669.1
-----------	----------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	136 g
Package 1 Height	60 mm
Package 1 width	80 mm
Package 1 Length	125 mm

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
