

Product data sheet

Characteristics

C2032VA-WE

Classic C2000 Series, Flush Switch 2 Gang,
250VAC, 10A, Classic , Standard, Vertical



Main

| | |
|---------------------|--|
| Range of product | Classic Series C2000 |
| Product brand | Clipsal |
| Device presentation | Basic element with full cover plate and grid |

Complementary

| | |
|--------------------------------|--------------------------------|
| Switch function | 1-pole |
| Number of rocker | 2 |
| Number of poles | 1 |
| Device mounting | Flush |
| Fixing mode | By screws |
| Surface finish | Glossy |
| Local signalling | without |
| [Ue] rated operational voltage | 250 V AC |
| Rated current | 10 A 8 AX, fluorescent lamp |
| Marking | Without marking |
| Actuator | Rocker |

Environment

| | |
|-----------|----------------|
| Standards | AS/NZS 60669.1 |
|-----------|----------------|

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3 cm |
| Package 1 Width | 7.6 cm |
| Package 1 Length | 11.7 cm |
| Package 1 Weight | 76 g |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Compliant with Exemptions |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |