

Product data sheet

Characteristics

C2033VAPB-WE

SWITCH PUSH BUTTON 3 GANG VERTICAL



Main

Range of product	Impress Classic C2000 Series
Product or component type	Push-button
Colour	White electric
Product brand	Clipsal
Device presentation	Basic element with full cover plate





Complementary

Colour code	WE
Actuator	Push-button
Local signalling	Without light indicator
Fixing mode	By screws
Material	Plastic
[Ue] rated operational voltage	250 V AC
Inrush current	20 A
Depth	30 mm
Width	35 mm
Length	141 mm
Fixing center	122 mm
Mounting position	Vertical

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	114 g
Package 1 Height	45 mm
Package 1 width	115 mm
Package 1 Length	75 mm

Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	 RECh Declaration
RECh free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Environmental Disclosure

 [Product Environmental Profile](#)

Circularity Profile

 [End Of Life Information](#)
