

Product data sheet

Characteristics

C2034VA-WE

Flush Switch, Classic C2000 Series, 4 Gang,
250VAC, 10A, Standard, Vertical



Main

Range of product	Classic Series C2000
Product brand	Clipsal
Assembly Type	Basic element with full cover plate and grid

Complementary

Installation Type	Flush
Number Of Switches	4
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Mounting Type	By screws
Actuator	Rocker

Environment

Standards	AS/NZS 60669.1
-----------	----------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	7.6 cm
Package 1 Length	11.7 cm
Package 1 Weight	105 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	122 cm
Package 2 Width	141 cm
Package 2 Length	161 cm
Package 2 Weight	1.145 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations