

Product data sheet

Characteristics

C2036HA-WE

Clipsal C2000 Series Flush Switch 6 Gang, 250VAC, 10A, Classic , Standard, Horizontal



Main

Range of product	Classic Series C2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

Complementary

Number of rocker	6
Device mounting	Flush
Fixing mode	By screws
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Actuator	Rocker

Environment

Standards	AS/NZS 60669.1
-----------	----------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	7.6 cm
Package 1 Length	11.7 cm
Package 1 Weight	131 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	115 cm
Package 2 Width	85 cm
Package 2 Length	154 cm
Package 2 Weight	0.74 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	250 cm
Package 3 Width	214 cm
Package 3 Length	338 cm
Package 3 Weight	7.625 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile