

## Product data sheet

### Characteristics

# C325483AUX91

## Acti 9 MSC AUX9 Chassis for 1P MCB iC60 with 9mm Auxiliary - 3PH 250A 48P



### Main

Range	Acti 9
Device short name	MSC AUX9
Product or component type	Chassis
Device application	Distribution

### Complementary

Range compatibility	Acti 9 Isobar B distribution board
[In] rated current	250 A
Short-circuit withstand	25 kA 0.1 s
[Icw] rated short-time withstand current	25 kA
Number of ways	1 way (incomer) - 3P 48 ways (outgoer) - 1P with 9 mm
Length	650 mm
Width	215 mm
Busbar pitch	27 mm

### Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.