

## Product data sheet

### Characteristics

# C5032NL-WE

## KEY INPUT C-BUS 2 GANG LEARN



### Main

Product brand	Clipsal
Device presentation	Basic element with full cover plate
Colour	White electric







### Complementary

Control type	Button
Material	Plastic
[Ue] rated operational voltage	15...36 V DC
[In] rated current	18 mA
Mounting support	Wall
Colour code	WE

### Packing Units

Package 1 Weight	0.120 kg
Package 1 Height	46.000 mm
Package 1 width	88.000 mm
Package 1 Length	136.000 mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>