

## Product data sheet

### Characteristics

# CCT15721

## 1C Digital Time Switch, Acti9, 24 Hours + 7 Days



### Main

Range of product	Acti9
Product name	Acti9 IHP
Device short name	IHP
Product or component type	Programmable digital time switch
Device application	Building
Battery type	Lithium
Number of channels	1
Available equipment	Memory key
User language	French Portuguese English Italian Spanish German
Colour tint	White (RAL 9003)

### Complementary

Product compatibility	Mechanical compatibility with electrical distribution comb busbars
Power consumption in VA	4 VA
Maximum switching current	10 A - 250 V AC pf = 0.6 16 A - 250 V AC pf = 1
[Ue] rated operational voltage	230 V AC +/- 10 % at 50/60 Hz
Number of inputs	1 input(s) impulse and maintained
Accuracy	+/- 1 s/day 20 °C
Cycle duration	24 hours + 7 days
Maximum number of switchings	84
Minimum interval duration	1 s
Function available	Automatic winter/summer time changeover Pulse programming
Display type	Backlit LCD
Battery life	6 year(s)
Backup time	6 years time and program saving
Type of setting	Absence for holidays function Random function
Connections - terminals	Screwless terminals
Mounting support	DIN rail
9 mm pitches	5
Width	45 mm
Height	85 mm
Depth	66 mm
Function	Pulse programming and random function
Absence for holidays	Yes
Time changeover	Automatic
Updated by	None

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Compatibility code	IHP
Market segment	Small commercial

## Environment

Ambient air temperature for operation	-10...50 °C
IP degree of protection	IP20 B

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7 cm
Package 1 Width	8 cm
Package 1 Length	10.5 cm
Package 1 Weight	201 g

## Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------