

Product data sheet

Characteristics

CCT15854

Acti9 - IHP - 1C digital time switch - 24 hours + 7 days



Main

Range of product	Acti9
Product name	Acti9 IHP
Device short name	IHP
Product or component type	Programmable digital time switch
Device application	Building
Battery type	Lithium
Number of channels	1
Available equipment	Programming kit Memory key
Language	Portuguese English French Italian German Spanish
Colour tint	White (RAL 9003)

Complementary

Maximum switching current	16 A - 250 V AC pf = 1 4 A - 250 V AC pf = 0.6
[Ue] rated operational voltage	230 V AC - 15...10 % at 50/60 Hz
Accuracy	+/- 0.5 s/day 25 °C
Cycle duration	24 hours + 7 days
Maximum number of switchings	56
Minimum interval duration	1 min
Function available	Operating hours counter Automatic winter/summer time changeover
Display type	LCD
Battery life	10 year(s)
Backup time	10 years time and program saving
Type of setting	PIN code Absence for holidays function
Connections - terminals	2 x 0.5...2.5 mm ² screwless terminals
Mounting support	DIN rail
9 mm pitches	2
Width	18 mm
Height	90 mm
Depth	66 mm
Net weight	0.09 kg
Function	None
Absence for holidays	Yes
Time changeover	Automatic
Updated by	None
Compatibility code	IHP
Market segment	Residential Small commercial

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for operation	-25...55 °C
IP degree of protection	IP20 B

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	3.300 cm
Package 1 Width	8.300 cm
Package 1 Length	10.600 cm
Package 1 Weight	125.000 g
Unit Type of Package 2	Doboz
Number of Units in Package 2	86
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	11.366 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------