



Main

Product brand	Clipsal
---------------	---------

Complementary

[Ue] rated operational voltage	240 V AC
Air flow	260 m3/h
Diameter	200 mm impeller:
Power consumption in W	30 W
[In] rated current	0.21 A full load

Packing Units

Package 1 Weight	1301.000 g
Package 1 Height	128.000 mm
Package 1 width	128.000 mm
Package 1 Length	310.000 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.