

Product data sheet

Characteristics

CE200N

Exhaust fan, Airflow, ceiling, 200mm blade dia, white



Main

Range of product	Airflow
Range	Airflow
Product brand	Clipsal
Product or component type	Exhaust fan
Product destination	Ceiling fitting
Main colour tint	White
Colour tint	White

Complementary

Provided equipment	Fan 110 mm 200 mm
[Ue] rated operational voltage	230 V AC 50 Hz
Material	ABS (acrylonitrile butadiene-styrene)
Air flow	260 m ³ /h
Diameter	305 mm impeller:
Power consumption in W	30 W
[In] rated current	0.21 A full load
Plug & lead length	850 mm
Cut-out dimensions	240 mm diameter
Depth	110 mm
Motor type	Ball bearing
Number of blades	3
Noise level	45 dB
Fan type	Axial

Environment

IP degree of protection	IPx4
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	31 cm
Package 1 Width	12.5 cm
Package 1 Length	31 cm
Package 1 Weight	1.335 kg
Unit Type of Package 2	PAL
Number of Units in Package 2	72
Package 2 Height	114 cm
Package 2 Width	113 cm

Package 2 Length	113 cm
Package 2 Weight	120 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	3 Years
----------	---------