

Product data sheet

Characteristics

CEF30L-WE

Exhaust fan, ceiling-mount with LED grille white electric



Main

Range	Airflow
Product brand	Clipsal
Product or component type	Exhaust fan
Product destination	Ceiling fitting
Device application	Residential Commercial
Colour	White electric

Complementary

[Ue] rated operational voltage	240 V AC 50 Hz
Material	ABS + PC
Colour code	WE
Air flow	200 m3/h
Diameter	100 mm duct connection:
Power consumption in W	42 W

Environment

IP degree of protection	IP20
-------------------------	------

Packing Units

Package 1 Weight	3.100 kg
Package 1 Height	370.000 mm
Package 1 width	310.000 mm
Package 1 Length	220.000 mm

Contractual warranty

Warranty	2 years
----------	---------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.