

## Product data sheet

### Characteristics

# CEF40WK-WE

## Ducted Exhaust Fan Kit, Airflow, Airflow, Ceiling Mounted, 150mm



### Main

|                  |         |
|------------------|---------|
| Range of product | Airflow |
| Product brand    | Clipsal |

### Complementary

|                                |                  |
|--------------------------------|------------------|
| [Ue] rated operational voltage | 240 V            |
| Air flow                       | 290 m3/h         |
| Power consumption in W         | 35 W             |
| [In] rated current             | 0.15 A full load |

### Environment

|                         |      |
|-------------------------|------|
| IP degree of protection | IPx4 |
|-------------------------|------|

### Packing Units

|                              |       |
|------------------------------|-------|
| Unit Type of Package 1       | PCE   |
| Number of Units in Package 1 | 1     |
| Package 1 Height             | 31 cm |
| Package 1 Width              | 37 cm |
| Package 1 Length             | 37 cm |
| Package 1 Weight             | 4 kg  |

### Offer Sustainability

|                            |  |
|----------------------------|--|
| Sustainable offer status   | Green Premium product  |
| REACH Regulation           | <a href="#">REACH Declaration</a>  |
| EU RoHS Directive          | Compliant with Exemptions  |
| Mercury free               | Yes  |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                       |
| RoHS exemption information | <a href="#">Yes</a>  |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                |
| Circularity Profile        | No need of specific recycling operations <a href="#">Circularity Profile</a> |