

Product data sheet

Characteristics

CEF40WK-WE

FAN KIT CEILING DUCT 265



Main

Product brand	Clipsal
Colour	White electric

Complementary

[Ue] rated operational voltage	240 V
Colour code	WE
Air flow	290 m ³ /h
Power consumption in W	35 W
[In] rated current	0.15 A full load





Environment

IP degree of protection	IPx4
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	4 kg
Package 1 Height	310 mm
Package 1 width	370 mm
Package 1 Length	370 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile