

Product data sheet

Characteristics

CLITPBHS1

Clipsal - LED bulkhead - 20W - 1100 lm - 4000K - IP54 - grey body - rectangle



Main

Range	Clipsal
Product name	TPBH Series
Product or component type	Bulkhead
Device application	Lighting

Complementary

Type of installation	Outdoor
Total system power	20 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Colour rendering index	R _a =70
Luminous flux	1100 lm
Bulb lifespan	36000 h
Colour temperature	4000 K
Colour	Body: grey
Device mounting	DIN rail Surface
Mounting mode	Surface mounted
Shape	Rectangular
Length	220 mm
Width	130 mm
Depth	36 mm
Net weight	0.536 kg

Environment

IP degree of protection	IP54
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	702 g
Package 1 Height	58 mm
Package 1 width	166 mm
Package 1 Length	268 mm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile