

## Product data sheet

### Characteristics

# CLITPCL1C1

## Ceiling Light LED, 20W, Dimmable, 3K/4K/6K



### Main

Range	Clipsal
Product or component type	Ceiling light
Device application	Lighting
Market segment	Residential Small commercial

### Complementary

Device mounting	Surface
Shape	Round
Type of installation	Indoor
Rated power in W	20 W
Light source	LED
Total system power	240 V AC 50 Hz
Luminous flux	1300 Lm 3000 K 1300 Lm 4000 K 1300 Lm 6000 K
Colour rendering index	R <sub>a</sub> =80
Bulb lifespan	30000 h
Beam angle	120 °
Load type	Dimmable LED
Device composition	Round white metal and plastic fixed integral dimming driver soft glow Light diffuser
Quantity per set	1
Trim width	330 mm
Trim height	80 mm
Net weight	1.0 kg

### Environment

IP degree of protection	IP20
Unified glare rating	< 22
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	37.5 cm
Package 1 Length	37.5 cm
Package 1 Weight	1 kg