

Product data sheet

Characteristics

CLITPDB1

Clipsal Lighting, Batten Diffused LED, 600mm



Main

Range	Clipsal
Product name	TPDB Series
Product or component type	Batten light
Device application	Lighting

Complementary

Type of installation	Indoor/outdoor
Total system power	20 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	2000 lm
Bulb lifespan	30000 h
Colour	White
Colour temperature	4000 K
Mounting mode	Ceiling
IP degree of protection	IP20
Electrical insulation class	Class I
Length	570 mm
Width	72 mm
Height	72.5 mm
Shape	Rectangular
Net weight	1.2 kg

Environment




Colour rendering index	R _a =80
Ambient air temperature for operation	-10...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	7.7 cm
Package 1 Length	61.6 cm
Package 1 Weight	1.2 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	6
Package 2 Height	17.0 cm

Package 2 Width	26.0 cm
Package 2 Length	63.0 cm
Package 2 Weight	7.2 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes