

Product data sheet

Characteristics

CLITPDB2

LED diffused batten, Clipsal, 40W, 4000 K,
4000 lm, white



Main

Range	Clipsal
Product name	TPDB Series
Product or component type	Batten light
Device application	Lighting

Complementary

Type of installation	Indoor/outdoor
Total system power	40 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	4000 lm
Bulb lifespan	30000 h
Colour	White
Colour temperature	4000 K
Mounting mode	Ceiling
IP degree of protection	IP20
Electrical insulation class	Class I
Length	1170 mm
Width	72 mm
Height	72.5 mm
Shape	Rectangular
Net weight	1.8 kg

Environment

Colour rendering index	R _a =80
Ambient air temperature for operation	-10...45 °C
Relative humidity	10...95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	2.0 kg
Package 1 Height	7.5 cm
Package 1 width	7.7 cm
Package 1 Length	121.6 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	4

Package 2 Weight	8.3 kg
Package 2 Height	17 cm
Package 2 width	17.4 cm
Package 2 Length	123 cm