

Product data sheet

Characteristics

CLITPDB2EM

Clipsal Lighting, Batten Diffused LED, 1200mm, Emerg



Main

Range	Clipsal
Product name	TPDB Series
Product or component type	Batten light
Device application	Lighting
Battery type	LiFePO4

Complementary

Type of installation	Indoor/outdoor
Operational power in W	40 W
Light source	LED
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	4000 lm
Bulb lifespan	30000 h
Colour	White
Colour temperature	4000 K
Autonomy	3 h
Charging time	16 h
Control type	Test button
Supply	Non-maintained
Device mounting	Surface
Mounting mode	Ceiling
IP degree of protection	IP20
Electrical insulation class	Class I
Length	1170 mm
Width	72.5 mm
Height	72 mm
Shape	Rectangular
Distance between centers	1170 mm
Net weight	2.2 kg

Environment

Colour rendering index	R _a =80
Ambient air temperature for operation	-10...45 °C
Relative humidity	10...95 %
Targeted country	Australia

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	7.7 cm
Package 1 Length	121.6 cm
Package 1 Weight	2.4 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	17.0 cm
Package 2 Width	17.4 cm
Package 2 Length	123.0 cm
Package 2 Weight	10.0 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes