

Product data sheet

Characteristics

CLITPDBLED1

Clipsal, Diffused Batten LED, 20W, 600mm, 4000K



Main

Range	Clipsal
Product or component type	Batten light
Device application	Lighting
Market segment	Small commercial Residential

Complementary

Type of installation	Indoor
Total system power	21 W
Power factor	0.9
Light source	LED 40 W
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	1900 lm
Bulb lifespan	50000 h
Colour temperature	4000 K
Beam angle	105 °
Device mounting	Surface
Mounting mode	Surface mounting
IP degree of protection	IP20
Electrical insulation class	Class I
Length	630 mm
Width	80 mm
Height	85 mm
Shape	Rectangular
Net weight	1.2 kg

Environment




Colour rendering index	R _a =80
Ambient air temperature for operation	-10...50 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	9.0 cm
Package 1 Length	67.5 cm
Package 1 Weight	1.5 kg

Unit Type of Package 2	CAR
Number of Units in Package 2	6
Package 2 Height	29.0 cm
Package 2 Width	20.0 cm
Package 2 Length	70.0 cm
Package 2 Weight	7.834 kg

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes

Contractual warranty

Warranty	3-Year
----------	--------