

## Product data sheet

### Characteristics

## CLITPDBLED2

Clipsal, LED diffused batten light - 42W - 3800  
lm - 4000K - 1200mm



### Main

Range	Clipsal
Product name	TPDB Series
Product or component type	Batten light
Device application	Lighting
Market segment	Small commercial Residential

### Complementary

Type of installation	Indoor
Total system power	42 W
Power factor	0.9
Light source	LED 40 W
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	3800 lm
Bulb lifespan	50000 h
Colour temperature	4000 K
Beam angle	105 °
Mounting mode	Clip-on
IP degree of protection	IP20
Length	1230 mm
Width	80 mm
Height	85 mm
Diameter	300 mm
Mounting Centers	945 mm
Net weight	1.8 kg




### Environment

Colour rendering index	R <sub>a</sub> =80
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...85 % non-condensing

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	9.0 cm
Package 1 Length	126.0 cm
Package 1 Weight	2.1 kg

Offer Sustainability

REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>
RoHS exemption information	 <a href="#">Yes</a>