

Product data sheet

Characteristics

CLITPDBSLED2

Architectural Batten LED, 40W, 1200mm, 4000K



Main

Range	Clipsal
Product or component type	Batten light
Device application	Lighting
Market segment	Small commercial Residential

Complementary

Type of installation	Indoor
Total system power	40 W
Power factor	0.9
Light source	LED 40 W
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	4800 lm
Bulb lifespan	36000 h
Colour temperature	4000 K
Beam angle	110 °
Device mounting	Surface
Mounting mode	Surface mounting
IP degree of protection	IP20
Electrical insulation class	Class I
Length	1215 mm
Width	120 mm
Height	30 mm
Shape	Rectangular
Net weight	3.0 kg

Environment

Colour rendering index	R _a =80
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

Contractual warranty

Warranty	3-Year
----------	--------