

Product data sheet

Characteristics

CLITPDBSLED2

Architectural Batten LED, Clipsal - Lighting, 40W, 1200mm, 4000K

Main

Range	Clipsal
Product or component type	Batten light
Device application	Lighting
Market segment	Small commercial Residential

Complementary

Type of installation	Indoor
Total system power	40 W
Power factor	0.9
Light source	LED 40 W
[Ue] rated operational voltage	240 V AC 50 Hz
Luminous flux	4800 lm
Bulb lifespan	36000 h
Colour temperature	4000 K
Beam angle	110 °
Device mounting	Surface
Mounting mode	Surface mounting
IP degree of protection	IP20
Electrical insulation class	Class I
Length	1215 mm
Width	120 mm
Height	30 mm
Shape	Rectangular
Net weight	3.0 kg

Environment

Colour rendering index	R _a =80
Ambient air temperature for operation	-10...40 °C
Relative humidity	10...95 % non-condensing

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.7 cm
Package 1 Width	12.6 cm
Package 1 Length	123 cm
Package 1 Weight	3 kg

Contractual warranty

Warranty

3-Year
